


# SUMMIT™ SERIES FACILITY PLANNER

500 & 750KVA/480V INPUT  
OUTPUT/60HZ



SUMMIT UPS MAIN INPUT DATA				SUMMIT UPS BYPASS INPUT DATA	
UPS RATING (KVA)/(kW)	UPS INPUT POWER (kVA)/(kW)	UPS INPUT CURRENT NOM/MAX (A)	MAIN (BIN) EXTERNAL OVERCURRENT PROTECTION (A)	UPS BYPASS CURRENT (A)	UPS BYPASS EXTERNAL OVERCURRENT PROTECTION (A)
500/500	512/512	615/677	800 (100% RATED)	601	800
750/750	768/769	923/1,015	1,200 (100% RATED)	902	1,200
NOTES	1,2,3,4	5	2,6,7	7	2,6,7

SUMMIT UPS OUTPUT DATA			BATTERY SYSTEM DATA	
UPS RATING (KVA)/(kW)	UPS OUTPUT CURRENT (A)	UPS OUTPUT EXTERNAL OVERCURRENT PROTECTION (A)	BATTERY SYSTEM OUTPUT CURRENT AT 400VDC END VOLTAGE (A)	BATTERY CABINET OVERCURRENT PROTECTION (A)
500/500	601	800	1,282	600
750/750	902	1,200	1,923	600
NOTES	10,11,12	2,8	2,9	2

MECHANICAL DATA				
UPS RATING (KVA)	DIMENSIONS (W X D X H) (INCHES)	WEIGHT (LBS)	DISTRIBUTED FLOOR LOADING (LBS/FT <sup>2</sup> )	POINT LOADING (LBS/FT <sup>2</sup> )
500	59.1 X 33.8 X 80.6	2,772	200	2,030
750	84.6 X 33.8 X 80.6	3,990	200	1,535
NOTES	16	2		15

HEAT LOSS AND AIR FLOW				
UPS RATING (KVA)	HEAT REJECTION (kBTU/Hr)			AIR FLOW REQUIREMENTS (CFM)
	100%	75%	50%	
500	42.0	26.1	17.4	
750	62.9	39.2	26.1	
NOTES	13,14			1



www.MitsubishiCritical.com  
UPSSales@meppi.com  
800-887-7830

1. Acceptable input and bypass voltage range is 480VAC, +15%, -20%
2. Install and ground the UPS system in accordance with NFPA 70 National Electrical Code and all federal, state and local regulations.
3. UPS main input and bypass frequency: 60Hz  $\pm$  10%.
4. UPS input power factor: 0.99 at 100% load and 0.99 at 50% load. The UPS input power factor is independent of the UPS output (load) power factor.
5. The nominal current is continuous and is based on 100% load. The maximum current includes the nominal input current at 100 % load and the non-continuous battery recharge current. Consult factory before operating at the maximum current.
6. Power main input and bypass feeder inputs (provided by others) from separate overcurrent protection devices. Main input overcurrent protection devices are sized based on the maximum current which includes the maximum battery charging current.
7. Main Input and bypass input are 3-phase, 3-wire plus ground. UPS cable entry cabinet has top or bottom conduit entry.
8. UPS output overcurrent protection device is provided by others. UPS output cables are to be run conduits separate from the input and bypass cables: 3-phase, 3-wire plus ground.
9. Consult the factory when using a non-lead acid battery stored energy system.
10. UPS inverter output voltage regulation:  $\pm$ 1% balanced load,  $\pm$ 2% unbalanced load.
11. UPS output total harmonic voltage distortion (THDv):  $\leq$ 2% at 100% linear load and  $\leq$ 5% at 100% nonlinear load.
12. Maximum load crest factor: 2.1.
13. The specified heat losses are only for the UPS module. Peripheral equipment heat losses must be considered separately.
14. Maintain clearances per the UPS installation drawing. Minimum overhead clearance: 23.6 inches.
15. Use point loading with raised-floor installations.
16. Includes cable entry cabinet.

